



**Cup brush 65x0.35 mm/ M 14, steel-wire, twisted, 50 units (23796), packed loose, wire thickness 0.35 mm**

- For universal use in metal processing, e.g. for cleaning, deburring, purging, removing rust, smoothing welding seams and points, stripping slag, scales and old paint
- For processing large areas, weld seams etc.
- Edging type: twisted steel wire

<b>Order no.</b>	<b>623796700</b>
<b>EAN code</b>	<b>4007430435088</b>
Diameter	65 mm / 2 3/4 "
Female thread	M 14
Wire thickness	0.35 mm
Maximum speed	11000 rpm
Sales unit / packaging unit	1 / 50