



**Cup brush 65x0.35 mm/M 14, stainless steel wire, twisted, stainless, wire thickness 0.35 mm**

- For universal use in stainless steel processing, e.g. for smoothing welding seams and points, stripping slag, scales and old paint. Ideally suited for processing stainless steels
- Edging type: twisted stainless steel wire

<b>Order no.</b>	<b>623801000</b>
<b>EAN code</b>	<b>4007430408266</b>
Diameter	65 mm / 2 3/4 "
Female thread	M 14
Wire thickness	0.35 mm
Maximum speed	11000 rpm
Sales unit / packaging unit	1 / 1