



Flap disc 178 mm P 120, zirconia alumina, steel, stainless steel, curved type

- Suitable for rough and intermediate grinding in all fields of metalworking including stainless steel, steel, cast iron, and sheet steel
- High lamellar lining on fibreglass pad
- Uniform grinding capacity
- Cool grinding
- Low noise level
- Uniform grinding result, comfortable grinding with only low vibration
- Most suitable for processing stainless steels
- Maximum working speed 80 m/s; flap disc in slanted version; angle of attack 7-9°

| | |
|-----------------------------|-----------------------------|
| Order no. | 624276000 |
| EAN code | 4007430085535 |
| Diameter x bore | 178 x 22.23 mm // 7 x 7/8 " |
| Grit | P 120 |
| Version | sloping |
| Maximum speed | 8500 rpm |
| Sales unit / packaging unit | 1 / 10 |