



**Flap disc 125 mm P 60, zirconia alumina, steel, stainless steel, curved type**

- Suitable for rough and intermediate grinding in all fields of metalworking including stainless steel, steel, cast iron, and sheet steel
- High lamellar lining on fibreglass pad
- Uniform grinding capacity
- Cool grinding
- Low noise level
- Uniform grinding result, comfortable grinding with only low vibration
- Most suitable for processing stainless steels
- Maximum working speed 80 m/s; flap disc in slanted version; angle of attack 7-9°

<b>Order no.</b>	<b>624277000</b>
<b>EAN code</b>	<b>4007430433008</b>
Diameter x bore	125 x 22.23 mm // 5 x 7/8 "
Grit	P 60
Version	sloping
Maximum speed	12200 rpm
Sales unit / packaging unit	1 / 10