



**Flap disc 115 mm P 80, aluminium oxide, steel, non-ferrous metals, curved type**

- Suitable for rough and intermediate grinding of steel, non-ferrous metals, wood and plastics
- High lamellar lining on fibreglass pad
- Uniform grinding capacity
- Cool grinding
- Low noise level
- Uniform grinding result, comfortable grinding with only low vibration
- Maximum working speed 80 m/s
- Tilted version: angle of attack 7-9°

<b>Order no.</b>	<b>624393000</b>
<b>EAN code</b>	<b>4007430444066</b>
Diameter x bore	115 x 22.23 mm
Grit	P 80
Version	sloping
Maximum speed	13300 rpm
Sales unit / packaging unit	1 / 10