



HSS-R drill bit 14.0 x 160 mm, with offset shank

- Spiral drill bit made of high-grade high-speed steel according to DIN 338, roll-milled, cylindrical, right-hand cutting, type N
- Cone-shaped shell polished surface 118°, diameter tolerance h8
- Black surface
- Suitable for drilling in steel, non-ferrous metals, alloyed and non-alloyed cast steel. Up to 900 N/mm² tensile strength.

Order no.	625007000
EAN code	4007430100573
Diameter	14 mm
Overall length	160 mm
Working length	108 mm
Shaft Ø	10 mm
Sales unit	1