



### HSS-G drill bit 2.0x85 mm, DIN 340

- Precision spiral drill bit made of high-grade high-speed steel according to DIN 340, ground from the solid, long, cylindrical, right-hand cutting, type N, crosswise grinding 135° according to DIN 1412 C (from 3 mm), diameter tolerance h8
- Bare surface
- For highest demands and precision in industry and handcraft
- For drilling steels, cast steel, alloyed and unalloyed, grey cast iron, ductile cast iron, sintered iron, nickel silver, graphite. Up to 900 N/mm<sup>2</sup> tensile strength.

|                  |                      |
|------------------|----------------------|
| <b>Order no.</b> | <b>625031000</b>     |
| <b>EAN code</b>  | <b>4007430100702</b> |
| Diameter         | 2 mm                 |
| Overall length   | 85 mm                |
| Working length   | 56 mm                |
| Sales unit       | 1                    |