



### HSS-G drill bit 7.0x156 mm, DIN 340

- Precision spiral drill bit made of high-grade high-speed steel according to DIN 340, ground from the solid, long, cylindrical, right-hand cutting, type N, crosswise grinding 135° according to DIN 1412 C (from 3 mm), diameter tolerance h8
- Bare surface
- For highest demands and precision in industry and handcraft
- For drilling steels, cast steel, alloyed and unalloyed, grey cast iron, ductile cast iron, sintered iron, nickel silver, graphite. Up to 900 N/mm<sup>2</sup> tensile strength.

<b>Order no.</b>	<b>625053000</b>
<b>EAN code</b>	<b>4007430100924</b>
Diameter	7 mm
Overall length	156 mm
Working length	102 mm
Sales unit	1