



HSS-G drill bit 13.0x205 mm, DIN 340

- Precision spiral drill bit made of high-grade high-speed steel according to DIN 340, ground from the solid, long, cylindrical, right-hand cutting, type N, crosswise grinding 135° according to DIN 1412 C (from 3 mm), diameter tolerance h8
- Bare surface
- For highest demands and precision in industry and handcraft
- For drilling steels, cast steel, alloyed and unalloyed, grey cast iron, ductile cast iron, sintered iron, nickel silver, graphite. Up to 900 N/mm² tensile strength.

Order no.	625066000
EAN code	4007430101051
Diameter	13 mm
Overall length	205 mm
Working length	134 mm
Sales unit	1