



## SDS-Plus Pro 4 hammer drill bit / 6.5 x 450 mm

- Highest drill speed thanks to reduction in friction and improved impact transmission thanks to the special cutting geometry on the chisel-shaped drill head.
- Stable and durable centering point for high-precision spot-drilling
- Power breakers cause micro tears in the material for a noticeable quicker drill progress
- The probability of snagging on concrete reinforcements is significantly reduced thanks to enlarged armouring phases.
- The 2-spiral helix with its helical geometry with reinforced core ensures quick delivery of bore dust and maximum breakage resistance
- For use in concrete, masonry, natural stone, granite

<b>Order no.</b>	<b>625119000</b>
<b>EAN code</b>	<b>4061792171145</b>
Diameter	6.5 mm
Working length	390 mm
Overall length	450 mm
Sales unit	1