



10 SDS-Plus Pro 4 hammer drill bits / 8.0 x 110 mm

- Highest drill speed thanks to reduction in friction and improved impact transmission thanks to the special cutting geometry on the chisel-shaped drill head.
- Stable and durable centering point for high-precision spot-drilling
- Power breakers cause micro tears in the material for a noticeable quicker drill progress
- The probability of snagging on concrete reinforcements is significantly reduced thanks to enlarged armouring phases.
- The 2-spiral helix with its helical geometry with reinforced core ensures quick delivery of bore dust and maximum breakage resistance
- For use in concrete, masonry, natural stone, granite

| | |
|-----------|---------------|
| Order no. | 625236000 |
| EAN code | 4007430103567 |

| | |
|----------------|--------|
| Diameter | 8 mm |
| Working length | 50 mm |
| Overall length | 110 mm |
| Sales unit | 10 |