



10 SDS-Plus Pro 4-hammer drill bits / 10.0 x 210 mm

- Highest drill speed thanks to reduction in friction and improved impact transmission thanks to the special cutting geometry on the chisel-shaped drill head.
- Stable and durable centering point for high-precision spot-drilling
- Power breakers cause micro tears in the material for a noticeable quicker drill progress
- The probability of snagging on concrete reinforcements is significantly reduced thanks to enlarged armouring phases.
- The 2-spiral helix with its helical geometry with reinforced core ensures quick delivery of bore dust and maximum breakage resistance
- For use in concrete, masonry, natural stone, granite

Order no.	625241000
EAN code	4007430103611

Diameter	10 mm
Working length	150 mm
Overall length	210 mm
Sales unit	10