



## 10 SDS-Plus Pro 4-hammer drill bits / 12.0 x 160 mm

- Highest drill speed thanks to reduction in friction and improved impact transmission thanks to the special cutting geometry on the chisel-shaped drill head.
- Stable and durable centering point for high-precision spot-drilling
- Power breakers cause micro tears in the material for a noticeable quicker drill progress
- The probability of snagging on concrete reinforcements is significantly reduced thanks to enlarged armouring phases.
- The 2-spiral helix with its helical geometry with reinforced core ensures quick delivery of bore dust and maximum breakage resistance
- For use in concrete, masonry, natural stone, granite

<b>Order no.</b>	<b>625243000</b>
<b>EAN code</b>	<b>4007430103635</b>

Diameter	12 mm
Working length	110 mm
Overall length	160 mm
Sales unit	10