



### Fibre disc 115 mm P 80, ceramic grain

- Self-sharpening ceramic grain for extremely high material removal with little effort
- Excellent results for surface grinding of steel and stainless steel. Ideal for extreme grinding jobs such as processing high-alloy steels, titanium alloys, nickel-based alloys as well as chromium and chromium-nickel steels, brass and bronze, thanks to high load capacity.
- Very high tool life; cool grinding
- Ceramic filter discs achieve their best performance on powerful angle grinders with increased down pressure.
- Fibre discs for clamping on backing pad! The backing pads with cooling fins are recommended for clamping the ceramic fibre sanding discs (e.g. Ø 125 mm, 623291000)
- Maximum working speed 80 m/s

<b>Order no.</b>	<b>626153000</b>
<b>EAN code</b>	<b>4007430217929</b>
Diameter x bore	115 x 22.23 mm // 4 1/2 x 7/8 "
Grit	P 80
Maximum speed	13300 rpm
Sales unit / packaging unit	1 / 25