



10 Sanding belts 40 x 760 mm, P60, ceramic grain, for pipe belt sanders

- For all metal uses, particularly suited for processing stainless steels/Inox. Flexible high performance sanding belt, semi-open coarseness with cotton base
- Extremely high material removal with extremely high tool life thanks to the self-sharpening ceramic grain. Even grinding and best results.
- For pre-polishing and fine polishing, for example, of contours, profiles, etc.
- Recommended circumferential speed: 25-35 m/s for stainless steel
- Recommended circumferential speed: 20-30 m/s for NF metals
- Recommended circumferential speed: 5-10 m/s for high temperature Ni-/Co steels

Order no.	626308000
EAN code	4007430194794

Dimensions	40 x 760 mm // 1 9/16 x 30 "
------------	------------------------------

Grit	P 60
------	------

Sales unit	10
------------	----