



**Carbide core drill 25x55 mm, Weldon shank  
19 mm (3/4")**

- Core drill Ø 14 - 60 mm with Weldon shank 19 mm (3/4")
- Core drill as of Ø 70 mm with Weldon shank 32 mm (1 1/4")
- Insert only with suitable centring pin
- Also suitable for higher alloyed steels

<b>Order no.</b>	<b>626582000</b>
<b>EAN code</b>	<b>4007430198310</b>
Diameter	25 mm
Overall length	90 mm / 3 9/16 "
Working length	55 mm / 2 1/8 "