



**Carbide core drill 38x55 mm, Weldon shank
19 mm (3/4")**

- Core drill Ø 14 - 60 mm with Weldon shank 19 mm (3/4")
- Core drill as of Ø 70 mm with Weldon shank 32 mm (1 1/4")
- Insert only with suitable centring pin
- Also suitable for higher alloyed steels

Order no.	626595000
EAN code	4007430198457
Diameter	38 mm
Overall length	90 mm / 3 9/16 "
Working length	55 mm / 2 1/8 "