



HSS-G drill bit set SP, 8 pieces

- HSS-G Metal drill bits, ground version, cylindrical, DIN 338, type N, 135° crosswise grinding, blank surface. Up to 900 N/mm² tensile strength
- Suitable for drilling holes in steel and cast steel, alloyed and unalloyed, grey cast iron, malleable cast iron, ductile cast iron, sintered iron, nickel silver, graphite, NF metals, plastic
- Content: 1x Ø2x49mm, 1x Ø3x61mm, 1x Ø4x75mm, 1x Ø5x86mm, 2x Ø6x93mm, 1x Ø7x109mm, 1x Ø8x117mm
- 8 pieces, in high-quality, robust plastic cassette in special Metabo design with extendable Euro hole punch
- When purchasing 12 x HSS-G drill bit boxes, automatic delivery in counter display!

Order no.
EAN code

626695000
4061792235335