



## Cutting dust extraction shroud CED 125 Plus

- Extraction shroud with plunge function and optimised flow channel for particularly low-dust cutting both indoors and outdoors
- Compact construction form table can be removed without tools for more flexibility when working close to walls and improved visibility for freehand cuts
- Cutting depth can be adjusted without tools. Max. cutting depth for freehand cuts is 27 mm, with table 25 mm, with precision guide rail 20 mm
- Robust sheet metal table for tilt-proof operation. Connection for dust extraction Ø 35/41 mm
- Anti-static plastic prevents electric charging and dust accumulations for a constantly high suction power
- Large, coloured operating elements for simple, tool-free adjustment, even when wearing gloves
- Sheet metal table with guide rollers for easy, precise feed. Protect delicate surfaces from scratches.
- Enables the use of a Metabo precision guide rail for cuts with great precision
- Scope of delivery incl. nut with two holes 5/8" and M 14.
- Cordless angle grinder: Suitable for W..18 LT BL 11-125, W..18 LTX BL 15-125 Quick
- Mains-powered angle grinder: Suitable for all Metabo angle grinders Ø125mm, except W 650, W 750, W.. 850, WQ 1000, W 1100, W 1150, WP 1200-125 RT, WEV 1500-125 RT, WE 1500-125 RT

Order no.	626731000
EAN code	4007430261977

Cutting disc Ø	115 / 125 mm
----------------	--------------

Maximum cutting depth	27 mm / 1 1/16 "
-----------------------	------------------