



## 5 Flexiarapid Super 76x1.0x10.0 mm Inox, TF 41

- The super-thin high-output disc especially for processing stainless steel
- Super quick with very long service life thanks to the use of special corundums
- Low in iron, sulphur and chlorine (Fe + S + Cl ≤ 0.1 %)
- For all rust and acid resistant steels (V2A, Nirosta, INOX), spring steels, tool steels
- For use in the manufacture of vehicles, containers, car bodies, consumer units etc.
- Cutting discs for quiet, precise cutting, cuts without burrs
- Hardness: hard
- Maximum working speed 80 m/s

<b>Order no.</b>	<b>626870000</b>
<b>EAN code</b>	<b>4061792174207</b>

Quality class	A 46-U
Diameter x thickness x bore	76 x 1 x 10 mm
Version	straight
Maximum speed	20100 rpm
Sales unit / packaging unit	5 / 1