



**Flap disc 76 mm P 80, zirconia alumina, steel, stainless steel, straight version**

- Suitable for rough and intermediate grinding in all fields of metalworking including stainless steel, steel, cast iron, and sheet steel
- High lamellar lining on fibreglass pad
- Uniform grinding capacity
- Cool grinding
- Low noise level
- Uniform grinding result, comfortable grinding with only low vibration
- Most suitable for processing stainless steels
- Maximum working speed 80 m/s; flap disc in slanted version; angle of attack 7-9°

|                             |                         |
|-----------------------------|-------------------------|
| <b>Order no.</b>            | <b>626876000</b>        |
| <b>EAN code</b>             | <b>4061792174269</b>    |
| Diameter x bore             | 76 x 10 mm // 3 x 0.4 " |
| Grit                        | P 80                    |
| Version                     | straight                |
| Maximum speed               | 20100 rpm               |
| Sales unit / packaging unit | 1 / 1                   |