



## HSS-G drill bit storage case, 19 pieces

- Precision spiral drill bit made of high-grade high-speed steel according to DIN 338, precision ground, cylindrical, right-hand cutting, type N
- 135° crosswise grinding according to DIN 1412 C (from 3 mm), diameter tolerance h8
- Bare surface
- For highest demands and precision in industry and handcraft
- For drilling steels, cast steel, alloyed and unalloyed, grey cast iron, ductile cast iron, sintered iron, nickel silver, graphite, non-ferrous metals, plastic. Up to 900 N/mm<sup>2</sup> tensile strength.
- 19 pieces, in robust plastic carry case
- Ø 1 / 1.5 / 2 / 2.5 / 3 / 3.5 / 4 / 4.5 / 5 / 5.5 / 6 / 6.5 / 7 / 7.5 / 8 / 8.5 / 9 / 9.5 / 10 mm

Order no.  
EAN code

627097000  
4007430071323