



## HSS-R drill bit storage case SP, 19 pieces

- HSS-R Metal drill bits, roll-milled version, cylindrical, type N, 118° cone-shaped, shell polished surface, 19 pieces, in metal case
- Ø 1 - 10 x 0.5 mm; Suitable for drilling in steel, non-ferrous metals, alloyed and non-alloyed cast steel. Up to 900 N/mm<sup>2</sup> tensile strength.

Order no.  
EAN code

627151000  
4007430175816