




HSS-R drill bit storage case SP, 25 pieces

- Metal drill bits, HSS-R, roll-milled version, cylindrical, type N, 118° cone-shaped, shell polished surface, 25 pieces, in metal case
- Ø 1 - 13 x 0.5 mm; Suitable for drilling in steel, non-ferrous metals, alloyed and non-alloyed cast steel. Up to 900 N/mm² tensile strength.
- 

Order no.
EAN code

627152000
4007430175823