



HSS-R drill bit storage case, 10 pieces

- Spiral drill bit made of high-grade high-speed steel according to DIN 338, roll-milled, cylindrical, right-hand cutting, type N
- Cone-shaped shell polished surface 118°, diameter tolerance h8
- Diameter tolerance h8
- Black surface
- Suitable for drilling in steel, non-ferrous metals, alloyed and non-alloyed cast steel. Up to 900 N/mm² tensile strength.
- 10 pieces, in plastic carry case
- Ø 1 / 2 / 3 / 4 / 5 / 6 / 7 / 8 / 9 / 10 mm

Order no.
EAN code

62715800
4007430071200