



HSS-R drill bit storage case, 25 pieces

- Spiral drill bit made of high-grade high-speed steel according to DIN 338, roll-milled, cylindrical, right-hand cutting, type N
- Cone-shaped shell polished surface 118°, diameter tolerance h8
- Diameter tolerance h8
- Black surface
- Suitable for drilling in steel, non-ferrous metals, alloyed and non-alloyed cast steel. Up to 900 N/mm² tensile strength.
- 25 pieces, in robust plastic storage case
- Ø 1 / 1.5 / 2 / 2.5 / 3 / 3.5 / 4 / 4.5 / 5 / 5.5 / 6 / 6.5 / 7 / 7.5 / 8 / 8.5 / 9 / 9.5 / 10 / 10.5 / 11 / 11.5 / 12 / 12.5 / 13 mm

Order no.
EAN code

627159000
4007430071309