



HSS-R drill bit storage case, 6 pieces

- Spiral drill bit made of high-grade high-speed steel according to DIN 338, roll-milled, cylindrical, right-hand cutting, type N
- Cone-shaped shell polished surface 118°, diameter tolerance h8
- Diameter tolerance h8
- Black surface
- Suitable for drilling in steel, non-ferrous metals, alloyed and non-alloyed cast steel. Up to 900 N/mm² tensile strength.
- 6 pieces, in plastic storage case
- Ø 2 / 3 / 4 / 5 / 6 / 8 mm

Order no.
EAN code

62716000
400743044462