



Futuro Top keyless chuck, 1.5 - 13 mm, R+L

- Suitable for cordless tools up to 70 Nm torque
- Impact-proof version; suitable for clockwise and anti-clockwise rotation
- Automatic re-tensioning flat jaw chuck
- Smooth running accuracy of up to 0.35 mm
- Suitable for reverse rotation up to maximum 50 Nm
- Suitable for all Metabo LTX-3 machines

Order no.	627198000
EAN code	4061792234994

Clamping width	1.5 - 13 mm
----------------	-------------