



2 HSS-CO drill bits 3.2x65 mm

- Precision spiral drill bit made of cobalt-alloyed high-grade high-speed steel according to DIN 338, precision-ground, cylindrical, type N, reinforced core thickness, with crosswise grinding 135° according to DIN 1412 C (from 2 mm), diameter tolerance h8
- Bronze surface
- For exceptional demands and precision work in handcraft and industry
- For drilling in steel, VA-steel, cast steel, non-ferrous metals, plastics, special alloys, chrome vanadium steel up to 1100 N/mm² tensile strength

| | |
|------------------|----------------------|
| Order no. | 627436000 |
| EAN code | 4007430068682 |
| Diameter | 3.2 mm |
| Overall length | 65 mm |
| Working length | 36 mm |
| Sales unit | 2 |