



## HSS-CO drill bit 4.1x75 mm

- Precision spiral drill bit made of cobalt-alloyed high-grade high-speed steel according to DIN 338, precision-ground, cylindrical, type N, reinforced core thickness, with crosswise grinding 135° according to DIN 1412 C (from 2 mm), diameter tolerance h8
- Bronze surface
- For exceptional demands and precision work in handcraft and industry
- For drilling in steel, VA-steel, cast steel, non-ferrous metals, plastics, special alloys, chrome vanadium steel up to 1100 N/mm<sup>2</sup> tensile strength

<b>Order no.</b>	<b>627440000</b>
<b>EAN code</b>	<b>4007430068781</b>
Diameter	4.1 mm
Overall length	75 mm
Working length	43 mm
Sales unit	1