



HSS-CO drill bit 7.0x109 mm

- Precision spiral drill bit made of cobalt-alloyed high-grade high-speed steel according to DIN 338, precision-ground, cylindrical, type N, reinforced core thickness, with crosswise grinding 135° according to DIN 1412 C (from 2 mm), diameter tolerance h8
- Bronze surface
- For exceptional demands and precision work in handcraft and industry
- For drilling in steel, VA-steel, cast steel, non-ferrous metals, plastics, special alloys, chrome vanadium steel up to 1100 N/mm² tensile strength

Order no.	627451000
EAN code	4007430068996
Diameter	7 mm
Overall length	109 mm
Working length	69 mm
Sales unit	1