



## Flexible shaft 27609

- Suitable for speeds of 20,000 to 30,000 rpm
- Bearing-mounted at both ends
- For router bits, mounted points, etc. with 6 mm shaft diameter. Interchangeable collet for accessories with 3 mm shaft diameter available as accessory (630715000)
- 6 mm driving shaft for fixing the flexible shaft in the collet bore of the drive machine. If the collet bore of the drive machine has a different dimension than 6 mm, the collet of the drive machine must be changed. 6 mm collet available as accessory (631945000)

<b>Order no.</b>	<b>627609000</b>
<b>EAN code</b>	<b>4007430413963</b>
Suitable for routers	FME 737
Suitable for die grinders	G 400 / GE 710 Compact / GE 710 Plus / GA 18 LTX
Length	1.3 m / 4 ft
Driving shaft	6 mm / 1/4 "
Collet bore	6 mm
Weight	0.8 kg / 1.76 lbs