



HSS-G plastic carry case SP, 25 pieces

- HSS-G Metal drill bits, ground version, cylindrical, DIN 338, type N, 135° crosswise grinding, blank surface, 25 pieces, in plastic carry case
- Ø 1 - 13 x 0.5 mm; Suitable for drilling steel and cast steel, alloyed and unalloyed, grey cast iron, malleable cast iron, ductile cast iron, sintered iron, nickel silver, graphite, non-ferrous metals, plastic; Up to 900 N/mm² tensile strength.

Order no.
EAN code

627669000
4007430332363