



## 10 HSS-R drill bits 4.9x86 mm

- Spiral drill bit made of high-grade high-speed steel according to DIN 338, roll-milled, cylindrical, right-hand cutting, type N
- Cone-shaped shell polished surface 118°, diameter tolerance h8
- Black surface
- Suitable for drilling in steel, non-ferrous metals, alloyed and non-alloyed cast steel. Up to 900 N/mm<sup>2</sup> tensile strength.

<b>Order no.</b>	<b>627739000</b>
<b>EAN code</b>	<b>4007430067494</b>
Diameter	4.9 mm
Overall length	86 mm
Working length	52 mm
Sales unit	10