



10 HSS-R drill bits 5.6x93 mm

- Spiral drill bit made of high-grade high-speed steel according to DIN 338, roll-milled, cylindrical, right-hand cutting, type N
- Cone-shaped shell polished surface 118°, diameter tolerance h8
- Black surface
- Suitable for drilling in steel, non-ferrous metals, alloyed and non-alloyed cast steel. Up to 900 N/mm² tensile strength.

| | |
|------------------|----------------------|
| Order no. | 627746000 |
| EAN code | 4007430067562 |
| Diameter | 5.6 mm |
| Overall length | 93 mm |
| Working length | 57 mm |
| Sales unit | 10 |