



10 HSS-R drill bits 6.0x93 mm

- Spiral drill bit made of high-grade high-speed steel according to DIN 338, roll-milled, cylindrical, right-hand cutting, type N
- Cone-shaped shell polished surface 118°, diameter tolerance h8
- Black surface
- Suitable for drilling in steel, non-ferrous metals, alloyed and non-alloyed cast steel. Up to 900 N/mm² tensile strength.

Order no.	627750000
EAN code	4007430067609
Diameter	6 mm
Overall length	93 mm
Working length	57 mm
Sales unit	10