



## 10 HSS-R drill bits 7.1x109 mm

- Spiral drill bit made of high-grade high-speed steel according to DIN 338, roll-milled, cylindrical, right-hand cutting, type N
- Cone-shaped shell polished surface 118°, diameter tolerance h8
- Black surface
- Suitable for drilling in steel, non-ferrous metals, alloyed and non-alloyed cast steel. Up to 900 N/mm<sup>2</sup> tensile strength.

|                  |                      |
|------------------|----------------------|
| <b>Order no.</b> | <b>627761000</b>     |
| <b>EAN code</b>  | <b>4007430067715</b> |
| Diameter         | 7.1 mm               |
| Overall length   | 109 mm               |
| Working length   | 69 mm                |
| Sales unit       | 10                   |