



10 HSS-R drill bits 8.1x117 mm

- Spiral drill bit made of high-grade high-speed steel according to DIN 338, roll-milled, cylindrical, right-hand cutting, type N
- Cone-shaped shell polished surface 118°, diameter tolerance h8
- Black surface
- Suitable for drilling in steel, non-ferrous metals, alloyed and non-alloyed cast steel. Up to 900 N/mm² tensile strength.

| | |
|------------------|----------------------|
| Order no. | 627771000 |
| EAN code | 4007430067814 |

| | |
|----------|--------|
| Diameter | 8.1 mm |
|----------|--------|

| | |
|----------------|--------|
| Overall length | 117 mm |
|----------------|--------|

| | |
|----------------|-------|
| Working length | 75 mm |
|----------------|-------|

| | |
|------------|----|
| Sales unit | 10 |
|------------|----|