



## 10 HSS-G drill bits 3.0x61 mm

- Precision spiral drill bit made of high-grade high-speed steel according to DIN 338, precision ground, cylindrical, right-hand cutting, type N, crosswise grinding 135° according to DIN 1412 C (from 3 mm), diameter tolerance h8
- Bare surface
- For highest demands and precision in industry and crafts.
- For drilling steels, cast steel, alloyed and unalloyed, grey cast iron, tempered cast iron, ductile cast iron, sintered iron, nickel silver, graphite, NF metals, plastic. Up to 900 N/mm<sup>2</sup> tensile strength.

<b>Order no.</b>	<b>627872000</b>
<b>EAN code</b>	<b>4007430064929</b>

Diameter	3 mm
----------	------

Overall length	61 mm
----------------	-------

Working length	33 mm
----------------	-------

Sales unit	10
------------	----