



10 HSS-G drill bits 4.1x75 mm

- Precision spiral drill bit made of high-grade high-speed steel according to DIN 338, precision ground, cylindrical, right-hand cutting, type N, crosswise grinding 135° according to DIN 1412 C (from 3 mm), diameter tolerance h8
- Bare surface
- For highest demands and precision in industry and crafts.
- For drilling steels, cast steel, alloyed and unalloyed, grey cast iron, tempered cast iron, ductile cast iron, sintered iron, nickel silver, graphite, NF metals, plastic. Up to 900 N/mm² tensile strength.

Order no.	627883000
EAN code	4007430065032

Diameter	4.1 mm
----------	--------

Overall length	75 mm
----------------	-------

Working length	43 mm
----------------	-------

Sales unit	10
------------	----