



10 HSS-G drill bits 5.0x86 mm

- Precision spiral drill bit made of high-grade high-speed steel according to DIN 338, precision ground, cylindrical, right-hand cutting, type N, crosswise grinding 135° according to DIN 1412 C (from 3 mm), diameter tolerance h8
- Bare surface
- For highest demands and precision in industry and crafts.
- For drilling steels, cast steel, alloyed and unalloyed, grey cast iron, tempered cast iron, ductile cast iron, sintered iron, nickel silver, graphite, NF metals, plastic. Up to 900 N/mm² tensile strength.

| | |
|------------------|----------------------|
| Order no. | 627892000 |
| EAN code | 4007430065124 |
| Diameter | 5 mm |
| Overall length | 86 mm |
| Working length | 52 mm |
| Sales unit | 10 |