



## 5 HSS-G drill bit 9.5x125 mm

- Precision spiral drill bit made of high-grade high-speed steel according to DIN 338, precision ground, cylindrical, right-hand cutting, type N, crosswise grinding 135° according to DIN 1412 C (from 3 mm), diameter tolerance h8
- Bare surface
- For highest demands and precision in industry and crafts.
- For drilling steels, cast steel, alloyed and unalloyed, grey cast iron, tempered cast iron, ductile cast iron, sintered iron, nickel silver, graphite, NF metals, plastic. Up to 900 N/mm<sup>2</sup> tensile strength.

<b>Order no.</b>	<b>627937000</b>
<b>EAN code</b>	<b>4007430065575</b>
Diameter	9.5 mm
Overall length	125 mm
Working length	81 mm
Sales unit	5