



## 10 HSS-G drill bits 3.1x65 mm

- Precision spiral drill bit made of high-grade high-speed steel according to DIN 338, precision ground, cylindrical, right-hand cutting, type N, crosswise grinding 135° according to DIN 1412 C (from 3 mm), diameter tolerance h8
- Bare surface
- For highest demands and precision in industry and crafts.
- For drilling steels, cast steel, alloyed and unalloyed, grey cast iron, tempered cast iron, ductile cast iron, sintered iron, nickel silver, graphite, NF metals, plastic. Up to 900 N/mm<sup>2</sup> tensile strength.

|                  |                      |
|------------------|----------------------|
| <b>Order no.</b> | <b>627972000</b>     |
| <b>EAN code</b>  | <b>4061792157903</b> |
| Diameter         | 3.1 mm               |
| Overall length   | 65 mm                |
| Working length   | 36 mm                |
| Sales unit       | 10                   |