



## HSS-G drill bit storage case, 7 pieces

- Precision spiral drill bit made of high-grade high-speed steel according to DIN 338, precision ground, cylindrical, right-hand cutting, type N
- 135° crosswise grinding according to DIN 1412 C (from 3 mm), diameter tolerance h8
- Bare surface
- For highest demands and precision in industry and handcraft
- For drilling steels, cast steel, alloyed and unalloyed, grey cast iron, ductile cast iron, sintered iron, nickel silver, graphite, non-ferrous metals, plastic. Up to 900 N/mm<sup>2</sup> tensile strength.
- 7-piece. in plastic carry case. Especially tailored drill bit set for rivet sizes of cordless blind rivet gun NP18 LTX BL 5.0
- Ø 2.5 / 3.1 / 2x 3.3 / 4.1 / 4.9 / 5.1 mm

Order no.  
EAN code

627979000  
4061792157385