



Saw blade "power cut wood - professional", 190x2.6/1.8x20, Z14 WZ 25°

- For coarse and semi-fine cuts with continuous feed. Ideal for high feed rate / low power consumption machines
- Good cutting results for straight cuts in solid wood
- Partially suitable for construction wood with nails and concrete residue
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel

Order no.	628004000
EAN code	4007430176158
Diameter x cutting width x bore	190 x 2.6 x 20 mm
Material	HW/CT
Number of teeth	14
Tooth shape	WZ
Steel blade thickness	1.8 mm
Rake angle	25°
Suitable for	Ks 1266 S / Ks 1468 S
Packaging	Cardboard box