



## Saw blade "power cut wood - professional", 230x2.6/1.8x30, Z18 FZ/FA 10°

- For coarse and semi-fine cuts with continuous feed. Ideal for high feed rate / low power consumption machines
- Good cutting results for straight cuts in solid wood
- Partially suitable for construction wood with nails and concrete residue
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel

<b>Order no.</b>	<b>628010000</b>
<b>EAN code</b>	<b>4007430177209</b>
Diameter x cutting width x bore	230 x 2.6 x 30 mm
Material	HW/CT
Number of teeth	18
Tooth shape	FZ/FA
Steel blade thickness	1.8 mm
Rake angle	10°
Suitable for	KS 85
Packaging	Cardboard box