



Saw blade "power cut wood - professional", 230x2.6/1.8x30, Z24 WZ 20°

- For coarse and semi-fine cuts with continuous feed. Ideal for high feed rate / low power consumption machines
- Good cutting results for straight cuts in solid wood
- Partially suitable for construction wood with nails and concrete residue
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel

| | |
|---------------------------------|----------------------|
| Order no. | 628011000 |
| EAN code | 4007430177216 |
| Diameter x cutting width x bore | 230 x 2.6 x 30 mm |
| Material | HW/CT |
| Number of teeth | 24 |
| Tooth shape | WZ |
| Steel blade thickness | 1.8 mm |
| Rake angle | 20° |
| Suitable for | KS 85 |
| Packaging | Cardboard box |