



## Saw blade "power cut wood - professional", 250x2.8/2.0x30, Z24 WZ 25°

- For coarse and semi-fine cuts with continuous feed. Ideal for high feed rate / low power consumption machines
- Good cutting results for straight cuts in solid wood
- Partially suitable for construction wood with nails and concrete residue
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel
- Secondary holder for circular saw blades with Ø 216, 250, 254 and over 300 mm

Order no.	628012000
EAN code	4007430177223
Diameter x cutting width x bore	250 x 2.8 x 30 mm
Material	HW/CT
Number of teeth	24
Tooth shape	WZ
Steel blade thickness	2 mm
Rake angle	25°
Suitable for	PKU 250 / PK 255 / PKF 255 / PKF 255 V8 / Multi 260 / Multi 310 / PK 250
Packaging	Cardboard box