



Saw blade "power cut wood - professional", 400x30, Z28 TZ 10° 10°

- For coarse and semi-fine cuts with continuous feed. Ideal for high feed rate / low power consumption machines
- Good cutting results for straight cuts in solid wood
- Partially suitable for construction wood with nails and concrete residue
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel
- Secondary holder for circular saw blades with Ø 216, 250, 254 and over 300 mm

Order no.	628018000
EAN code	4007430177384
Diameter x cutting width x bore	400 x 3.5 x 30 mm
Material	HW/CT
Number of teeth	28
Tooth shape	TZ
Steel blade thickness	2.5 mm
Rake angle	10°
Suitable for	BKS 400 Plus
Packaging	Cardboard box