



## Saw blade "power cut wood - professional", 254x2.4/1.6x30, Z24 WZ 20°

- For coarse and semi-fine cuts with continuous feed. Ideal for high feed rate / low power consumption machines
- Good cutting results for straight cuts in solid wood
- Partially suitable for construction wood with nails and concrete residue
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel
- Secondary holder for circular saw blades with Ø 216, 250, 254 and over 300 mm

<b>Order no.</b>	<b>628025000</b>
<b>EAN code</b>	<b>4007430229526</b>
Diameter x cutting width x bore	254 x 2.4 x 30 mm
Material	HW/CT
Number of teeth	24
Tooth shape	WZ
Steel blade thickness	1.6 mm
Rake angle	20°
Suitable for	TS 254 / TK 250 / TS 254 M
Packaging	Cardboard box